



ENGLISH

Datasheet

Stock No. 161-7257

RS PRO Vertical PDU 6 BS socket 3 m 32 A BS4343



IEC60309 plug 2P+E 32 A (BS4343)



SPECIFICATIONS:

Product Name: Designated Power Distribution Unit for Cabinet

Socket Type: BS1363 (90 degree) Outlet Module

Socket Quantity: 6

Power Input: Left end single input

Bracket Install: Inverse installation

Cable with plug: IEC60309 plug 2P+E 32 A (BS4343)

Control Function: No controlling function

Protection Function: 2017 hot swaps module

Case: Black

Cable Specification: 3 x 6.0 mm² x 3 M

Product Size: L x W x H =726 x 44.4 x 62 mm

Mounting Length: 700 mm

Case Length: 670 mm

Fittings: 2 pcs $\phi 6 \times 16$ mm cross bolt, 2 pcs M6 float nut, PDU manual, 1 pc 155 mm cover plate

Electrical Characteristics:

Rating voltage: 250 V ac 50/60 Hz

Rating Current: 32 A

Max. Power: 8000 W

Safety Authentication: CE

Operating Temperature: 0 - 50°C, relative humidity 0 - 95%

Applications:

PDU - Power Distribution Unit is widely used in network enclosure and server rack of data center in field of information technology, telecom, electric, power, finance and insurance, aviation, transportation, hospital, education, E-government etc.