

PRODUCT-DETAILS

# GRNY-250-9-C

## GROMMETING EXTD .25IN NAT NYL 100FT



### General Information

Extended Product Type	GRNY-250-9-C
Product ID	7TAG009750R0035
EAN	5414363023692
Catalog Description	GROMMETING EXTD .25IN NAT NYL 100FT
Long Description	Extruded Grommeting, Natural Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Height of 7.11mm (0.28 Inches), Width of 9.40mm (0.37 Inches), Thickness 1.27mm (0.05 Inches), Width Maximum Panel Thickness of 6.35mm (0.25 Inches), 30.48m (100 Foot) Reel

### Ordering

EAN	5414363023692
UPC	728494083261

### Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	15 in 381 mm
Package Level 1 Height	2.25 in 57 mm
Package Level 1 Depth / Length	21 in 533 mm
Package Level 2 Units	5 piece
Package Level 2 Width	12.5 in

Package Level 2 Height	318 mm 12 in
Package Level 2 Depth / Length	305 mm 18 in 457 mm

**Additional Information**

Brand / Label	Ty-Rap
Color	Natural
Effective Date	19960215
Material	Nylon/Polyamide 6.6
Number of Batteries	0
Panel Thickness	0.25 in 6.35 mm
Product Name	NYLON GROMMETING
Product Type	Grommeting
Special Functions	Used to line panel edges and knockouts where the chafing of wires is a concern.

**Certificates and Declarations (Document Number)**

Data Sheet, Technical Information	GRNY-250-9-C
Instructions and Manuals	GRNY-250-9-C

**Classifications**

ETIM 6	EC002604 - Cable bundle hose
ETIM 7	EC002604 - Cable bundle hose
UNSPSC	39131603
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5393 >> Grommet edging

**Categories**

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

