



ENGLISH

Datasheet

RS Pro 6 Digit, LCD, Counter, 10Hz, 85 → 265 V ac

RS Stock No: **896-7002**



Product Details

RS Pro counter with 6 digit LCD display, has frequency of 10 Hz and supply voltage of 85 to 265 V ac. This digital impulse counter is compact in size and suitable for panel mounting. It is designed with a large, easy-to-read display making the counter highly suitable for any counter application.

Features and Benefits

- 6-digit LCD display
- Compact size
- Panel mount
- Wide range of supply voltage
- Remote reset
- In-built non-volatile memory (EEPROM) offering exceptional reliability
- Lower power consumption

**Specifications:**

Approvals	RoHS Compliant
Count Mode	Pulse
Function	Impulse Counter
Meter Type	Electronic
Cutout Height	24 mm
Cutout Width	48 mm
Depth	36.5 mm
Maximum Count Frequency	10 Hz
Measurement Range	999999
Minimum Operating Temperature	-10°C
Number of Digits	6
Connection Type	Terminal
Cutout Size	48 x 24 mm
Display Type	LCD
Input Type	Voltage
Mounting Type	Flush/Panel Mount
Reset Method	Electrical
Supply Voltage	85 to 265 V ac