

B1004 - K-Step/K-Speed/K-Move/K-Start S1P HRO SRC

Collection: Kaptiv

Upper: Breathable Fabric

Insole: Wire Lace System

Lining: SmellStop Antiodor and Antibacterial*

Midsole: Fresh'n Flex

Toecap: Aluminium

Sole: Double-Density PU/HRO Rubber i-daptive® Technology

Outer Carton: 10

Kaptiv

The first safety footwear range with stability control, designed to offer incredible dynamic comfort.

Base

Comfort is what has inspired Base Protection since its first day of activity. The company produces safety footwear, combining technology and functional requirements, to respond to professional and more demanding clients.

Standards

EN ISO 20345: 2011 S1P (HRO SRC)



Features

- Anti-static footwear
- 200 joules resistant toe-cap
- Puncture resistant sole
- Shock absorption in the heel region
- Heat resistant 1 minute up to 300°C
- Hydrocarbons resistant
- Men's width
- Women's width
- Orthopaedic made to measure footbed, complying with european norms DGUV112-191

B1004 - K-Step/K-Speed/K-Move/K-Start S1P HRO SRC

Commodity Code: 6404199000

Test House

A.N.C.I. Servizi S.R.L (CIMAC) (Notified Body No.: NB: 0465)
Via Alberto Riva Villasanta, 3
, Italy
Cert No: N° F-113-05202-22

Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m³)	EAN13	GTIN/DUN14
B1004GBU36	Grey/Blue	67.0	41.0	36.0	1.1700	0.0989	8054633494332	
B1004GBU37	Grey/Blue	67.0	41.0	36.0	1.1790	0.0989	8054633494349	
B1004GBU38	Grey/Blue	67.0	41.0	36.0	1.2020	0.0989	8054633494356	
B1004GBU39	Grey/Blue	67.0	41.0	36.0	1.2530	0.0989	8054633493281	
B1004GBU40	Grey/Blue	67.0	41.0	36.0	1.2860	0.0989	8054633493298	
B1004GBU41	Grey/Blue	67.0	41.0	36.0	1.3390	0.0989	8054633493304	
B1004GBU42	Grey/Blue	67.0	41.0	36.0	1.3630	0.0989	8054633493311	
B1004GBU43	Grey/Blue	67.0	41.0	36.0	1.4260	0.0989	8054633493328	
B1004GBU44	Grey/Blue	67.0	41.0	36.0	1.4610	0.0989	8054633493335	
B1004GBU45	Grey/Blue	67.0	41.0	36.0	1.5040	0.0989	8054633493342	
B1004GBU46	Grey/Blue	67.0	41.0	36.0	1.5350	0.0989	8054633493359	
B1004GBU47	Grey/Blue	67.0	41.0	36.0	1.6180	0.0989	8054633493366	
B1004GBU48	Grey/Blue	67.0	41.0	36.0	1.6290	0.0989	8054633493373	