



ENGLISH

Datasheet

RS Pro Steel Alloy Compression Spring, 135mm x 27mm, 1.23N/mm

RS Stock No: **121-292**



Product Details

RS Pro stainless steel alloy compression spring measures 135 x 27 mm and has a spring rate of 1.23 N/mm. It handles a load of 127.49 N at a minimum working length of 31 mm. This spring features right hand helix construction.

Features and Benefits

- Wire diameter ends up to 0.8 mm are squared and ungrounded
- Wire diameter ends 1 mm and over are squared and ground
- Manufactured with a right hand helix



Specifications:

Ends	Closed (Square)/Ground
Material	Steel Alloy
Free Length	135 mm
Load at Minimum Working Length	127.49 N
Minimum Working Length	31 mm
Outside Diameter	27 mm
Spring Rate	1.23 N/mm
Wire Diameter	2 mm