



Fuse holder, low voltage, 20 A, AC 690 V, BS88/A1, 1P, BS, front connected, grey



Powering Business Worldwide™

Part no.

RED SPOT 20A FRONT CONNECTED-GREY

Catalog No.

RS20HGY

Delivery program

Product range			Fuse accessory
Basic function			Fuse-holder
Field of application			low voltage
Rated current	I	A	20
Rated voltage			AC 690 V
Construction size			BS88/A1
Description			front connected grey
Protection			IP20
Number of poles			1P
usable for size/applications			fuse-link NITD fuse-link NIT
Standard/Approval			BS
Standards/Regulations			BS88-2 IEC 60269-2

Technical data ETIM 7.0

Circuit breakers and fuses (EG000020) / Low Voltage HRC fuse base (EC000067)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse systems / Low-Voltage HRC fuse base (ecl@ss10.0.1-27-14-21-06 [AKE278013])			
Construction size			Other
Number of poles			1
Rated current		A	20
Bus-mounting type			No
Swivelling mechanism			No