



Sample photo

Order symbol: ABS 175/60 HT
Product nbr: 6081919
Description: Enclosure, ABS
Remarks: Smoked transparent cover

EAN: 6418074023216
El. number:
Finland 3420641
Denmark 8212023602
Italy 7362110
Sweden 2535863

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:				Rating:
	L	W	H	
mm:	180	180	60	Electrical insulation: Totally insulated Halogen free (DIN/VDE 0472, Part 815): Yes Flammability Rating (UL 746 C 5): UL 94 HB Glow Wire Test (IEC 695-2-1) °C: 650 NEMA Class: NEMA 1, 4, 4X, 6, 12, 13 Ingress Protection (EN 60529): IP 66/67 Impact Resistance (EN 50102): IK 07
inch:	7.1	7.1	2.4	
Materials:				
Material:	ABS			
Gasket material:	TPE			
Base colour:	RAL 7035			
Cover colour:	Smoked grey			
Cover screws material:	Polyamide			
Cover screws colour:	Black			
Temperatures:				
Short term:	-40 ... 80 °C			
Continuous:	-40 ... 60 °C			
Short term:	-40 ... 175 °F			
Continuous:	-40 ... 140 °F			
Accessories:				
MIV 175	Mounting plate (Galvanized steel)			
MIN 15	DIN-15 Mounting rail			
MIV 15	DIN-35 Mounting rail			
FP A 175/180	Front plate (Aluminium)			
HFP 180	Front plate hinge series (2 pcs)			
FP 22046	Wall fastening lug (4 pcs)			
Certificates:				
Fimko				
Europe EN 50298: 1998				
Gost R				

