



# PRODUCT DATASHEET

Datasheet creation date: 2025/07/09 7:37 (UTC)



## 629

### Extra Small Ball Bearings and Miniature Ball Bearings Metric Series



#### Boundary Dimensions

d	9	mm	Bore diameter
D	26	mm	Outside diameter
B	8	mm	Width
r (min.)	0.3	mm	Chamfer dimension

#### Basic Load Ratings

Cr	5050	N	Basic dynamic load rating
C0r	1970	N	Basic static load rating

#### Speeds

Grease	28000	min-1	Grease lubrication
Oil (Oil-bath)	34000	min-1	Oil-bath lubrication

#### Abutment and Fillet Dimensions

da (min.)	11	mm	Diameter of shaft abutment
Da (max.)	24	mm	Diameter of housing abutment
ra (max.)	0.3	mm	Radius of shaft or housing fillet

#### Additional information

z	7		Number of Balls
Dw	4.762	mm	Ball Diameter

#### Mass

Mass approx.	0.0195	kg	Mass approx.
--------------	--------	----	--------------

