

PC 5638



Sample image

Order symbol : PC 5638

Product nr : 6530807

Description : Base, PC

EAN : 6418074000491

El. number :

- Finland : 3423745
- Denmark : 8212006768
- Sweden : 2507810

Dimensions :	Height	Width	Depth
mm :	560	380	150
inch :	22.05	14.96	5.91

Materials :

Material :	Polycarbonate
Base colour :	RAL_7035

Ratings :

electrical_insulation :	Totally insulated
UV resistance :	UL 746C
Flammability Rating :	UL 94 5VA
Glow Wire Test (IEC 695-2-1) °C :	960C

Temperatures :

Temperature °C (continuous) :	-40 ... 80
Temperature °F (continuous) :	-40 ... 175