



Part Number : [1301530110](#)

Product Description : Super-Safeway In-Line Industrial GFCI, IP69K, Portable, Single Phase, Manual Reset, Flying Leads, 20A, 120V, 0.61m (2.0') Cord Length

Series Number : 130153

Status : Active

Product Category : Power Distribution

Engineering Number : 20051-0M



Documents & Resources

Drawings

[1301530110_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)4165-DC (25 June 2025)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power Distribution
Series	130153
Description	Super-Safeway In-Line Industrial GFCI, IP69K, Portable, Single Phase, Manual Reset, Flying Leads, 20A, 120V, 0.61m (2.0') Cord Length
Enclosure Rating	NEMA 4X
NEMA Configuration	N/A
Product Name	Super-Safeway
Type	GFCI Industrial Duty, Single Phase
UPC	78678889742

Agency

UL	E66308
----	--------

Electrical

Current - Maximum per Contact	20.0A
GFCI	Yes-In-line
GFCI Reset	Manual
Ground Continuity Monitor	No
Open Neutral Relay	Yes
Voltage - Maximum	120V

Physical

Cord Diameter	10.67mm (.420")
Cord Grip Body Size	Internal Double C-Clamp
Cord Length	0.61m (2.0')
Cord Type	12/3 SJEOOW

Feed-Thru	Yes
Flip Lid	No
Material - Housing	Nylon
Mounting Style	Portable
Net Weight	680.388/g
Number of Receptacles	0
Packaging Type	Bag
Receptacle Type	N/A

This document was generated on Nov 06, 2025