


HC-D 7-TFL-57/O1M20G

Order No.: 1604888



HEAVYCON sleeve housing D7, for single locking latch, height 57 mm, with support, straight conductor exit, zinc

Commercial data

GTIN (EAN)	 4 017918 881023
sales group	D011
Pack	10 pcs.
Customs tariff	85389099
Catalog page information	Page 574 (PC-2011)

Product notes

WEEE/RoHS-compliant since:
01/31/2006



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data**General data**

Note	For contact inserts HC-D7, D8, A3, A4, B5, HS2-D7
Design	D7
Height	57 mm
Width	28 mm

Length	26.5 mm
Housing type	Sleeve housings
Locking type	for single locking latch
No. of cable exits	1
Cable exit	Straight
Pg screw connection	None
Type of the screw connection	1x M20
Degree of protection for housing	IP54 / IP65 with sealing screw
Ambient temperature (operation)	-40 °C ... 125 °C
Housing material	Zinc die-cast
Housing surface material	Powder-coated, gray

Certificates / Approvals



Certification

GOST

Accessories

Item	Designation	Description
------	-------------	-------------

Assembly

1686229	HC-D 7-DS-IP65	Sealing screw, for IP65 protection
---------	----------------	------------------------------------

General

1647967	HC-M-DE-M20	Druckschrauben-Set, für Gehäuse mit M20-Gewinde und Stutzen, bestehend aus Einschnittdichtung, 2 Scheiben und Druckschraube, Kabeldurchmesser 4 - 13 mm, SW 20
---------	-------------	--

Diagrams/Drawings

Dimensioned drawing

