

## Rotary hammer with SDS-plus GBH 4-32 DFR Professional



### Rotary hammer with SDS-plus GBH 4-32 DFR Professional

The fastest multi-hammer  
in the 4kg class



#### Technical data

Rated power input	900 W
Max. impact energy	4,2 J
Impact rate at rated speed	0 – 3.600 bpm
Rated speed	0 – 800 rpm
Weight	4,7 kg
Toolholder	SDS-plus

#### Drilling range

Drilling diameter in concrete with hammer drill bits	6 – 32 mm
Max. drilling diameter in steel	13 mm
Max. drilling diameter in wood	32 mm

#### Functions

Forward/reverse operation	✓
Electronic	✓
Overload clutch	✓
Bosch SDS System	✓
Part number	0 611 332 171