



SOLID TANTALUM CHIP CAPACITORS - SURFACE MOUNT									
MODEL	CECC MIL SPEC. / TYPE	OUTLINE DRAWING	CAPACITANCE RANGE (μF)	WORKING VOLTAGES (W _{VDC})	8 mm TAPE	12 mm TAPE	16 mm TAPE	24 mm TAPE	BLISTER PACK
298D	-		1.0 to 220	4 to 25	M, P	-	-	-	-
293D 793DX CTC3 CTC4 793DE	- CECC 30801-005 CECC 30801-009 CECC 30801-011 CECC 30801-801		0.10 to 680	4 to 50	A, B, P	C, D, E	-	-	-
593D	-		0.47 to 680	4 to 50	A, B	C, D, E	-	-	-
TR3	-		0.47 to 680	4 to 50	A, B	C, D, E	-	-	-
TR8	-		1 to 220	4 to 16	P, M	-	-	-	-
TH3	-		0.35 to 100	10 to 50	A, B	C, D, E	-	-	-
TH5	-		10	21	E	-	-	-	-
595D	-		0.10 to 1500	4 to 50	T, A, S	B, C, D, G, H, M, R	-	-	-
594D	-		1.0 to 1500	4 to 50	-	B, C, D, R	-	-	-
592D	-		1.0 to 3300	4 to 35	A	B, C, D, R	-	X	-
591D	-		1.0 to 1000	4 to 35	A	B, C, D, R	-	-	-
572D	-		2.2 to 220	4 to 35	P, Q, S, A	B, T	-	-	-
597D	-		22 to 1500	4 to 50	-	V	E, R, F	-	-
195D	-		0.10 to 330	2 to 50	C, S, V	R, X, Y, Z	-	-	-
195D	-		0.10 to 100	2 to 50	A	B, D, E, F, G, H	-	-	-



SOLID TANTALUM CHIP CAPACITORS - SURFACE MOUNT									
MODEL	CECC MIL SPEC. / TYPE	OUTLINE DRAWING	CAPACITANCE RANGE (μF)	WORKING VOLTAGES (W _{VDC})	8 mm TAPE	12 mm TAPE	16 mm TAPE	24 mm TAPE	BLISTER PACK
695D	-		0.10 to 270	4 to 50	A	B, D, E, R, G	H	-	-
194D	CECC 30801-001		0.10 to 150	4 to 50	A	B, D, E, F	G, H	-	Y
T83	-		0.1 to 330	4 to 50	A, B	C, D, E	-	-	-
T95	-		0.1 to 680	4 to 50	-	B, C, D, R, S, V, X, Y, Z	-	-	-
T96	-		10 to 680	4 to 50	R	-	-	-	-
T97	-		10 to 1500	4 to 75	E, F, R, V, Z, D, M, H, N	-	-	-	-
T98	-		15 to 1500	4 to 63	E, F, R, V, Z, M, H	-	-	-	-
TP3	-		0.10 to 470	4 to 50	A, B, C, D, E	-	-	-	-
TM8	-		1 to 47	2 to 40	P, Q, L, R, W	D, E, F, N, T	-	-	-
CWR06	MIL-PRF-55365/4		0.10 to 100	4 to 50	A	B, C, D, E, F	G, H	-	-
CWR11	MIL-C-55365/8		0.10 to 100	4 to 50	A, B	D	-	-	-
CWR16	MIL-PRF-55365/13		0.33 to 330	4 to 35	A	B, C, D, E, F	G, H	-	-