

BIZ5 - Bizweld Work FR Coverall

Collection: Bizweld™ Work

Range: Flame Resistant Multi-Norm

Shell Fabric: Bizweld Work: 100% Cotton, 330g

Outer Carton: 12

Product information

The Bizweld FR Coverall offers visible protection to the wearer. Clever design features include flame resistant reflective tape on the shoulders, sleeves and legs, the option to insert knee pads when needed, ample storage space and a rule pocket. A very popular style.

Bizweld™ Work

Bizweld™ Work protective clothing have been specially designed to guarantee comfort, performance and safety whilst providing effective function at all times. Bizweld™ Work has been rigorously tested to ensure total compliance with the latest international standards.

Flame Resistant Multi-Norm

This industry leading flame resistant range provides multi-standard protection for hazardous environments. These state of the art products are the result of years of experience combined with advanced technology and market research. Commitment to the health, safety and comfort of the wearer can be seen in the wide range of products suitable for all climates and end uses.

Standards

EN ISO 11612 (A1+A2, B1, C1, E2, F1)

EN ISO 11611 Class 1 (A1+A2)

IEC 61482-2 IEC 61482-1-1 (ELIM 8.3 CAL/CM², ATPV 10.9 CAL/CM²)

ASTM F1959/F1959M-12 (ATPV 11.2 CAL/CM² (HAF = 80.4%))



Features

- Protection against radiant, convective and contact heat
- Certified protection against molten metal splash
- Two chest pockets with stud closure
- Rule pocket
- Concealed stud front for easy access
- Stud adjustable cuffs for a secure fit
- Available in sizes up to 5XL
- Two tier knee pad pockets allowing two positioning options
- 8 pockets for ample storage
- 40+ UPF rated fabric to block 98% of UV rays
- Radio loops for easy clipping of a radio

BIZ5 - Bizweld Work FR Coverall

Commodity Code: 6211321000

Test House

SATRA Technology Europe Ltd (Notified Body No.: NB: 2777)

Bracetown Business Park

D15 YN2P, Ireland

Cert No: 2777_12872_03_E00_00

Wash Care



Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	GTIN/DUN14
BIZ5NARXS	Navy	43.0	28.0	58.0	1.2710	0.0698	5036108243624	25036108731910
BIZ5NARS	Navy	43.0	28.0	58.0	1.3610	0.0698	5036108157303	25036108608946
BIZ5NARM	Navy	43.0	28.0	58.0	1.4390	0.0698	5036108157310	25036108608939
BIZ5NARL	Navy	43.0	28.0	58.0	1.4750	0.0698	5036108157327	25036108608922
BIZ5NARXL	Navy	43.0	28.0	58.0	1.5990	0.0698	5036108157334	25036108608953
BIZ5NARXXL	Navy	43.0	28.0	58.0	1.6410	0.0698	5036108157341	25036108608960
BIZ5NARXXXL	Navy	43.0	28.0	58.0	1.7960	0.0698	5036108157358	25036108608977
BIZ5NAR4XL	Navy	43.0	28.0	58.0	1.8210	0.0698	5036108157365	25036108608915
BIZ5NAR5XL	Navy	43.0	28.0	58.0	1.8390	0.0698	5036108216857	25036108703863