



Part No. 199112140

Series Compressed Air Hose Reels - Closed

3D PDF Inquiry List

# Category

Medium reel

Hose length on reel

10 m

Hose material

**PUR** 

Reel material

**Plastic** 

Weight

6.7 kg

ID x OD

11 x 16 mm

**Connection Inlet** 

R 1/2" Male

**Connection Outlet** 

## Max working pressure

12 bar

# Compressed Air Hose Reels - Closed

- · High flow and low pressure drop
- · Slow, strong retraction
- · Durable construction
- · Soft stop-ball prevents tripping.

The CEJN Safety Reel is a durable reel that provides excellent performance thanks to its full-flow patented design that, unlike most reels, does not restrict flow. This provides maximum power to the customer's tools, saving them both energy and time. This hose reel is ideal for a safe workplace. The slow retraction function, hose guiding, PUR hose, soft stop-ball to prevent tripping and anti-kink safety features are just a few examples of what makes these safety reels the best on the market. The reel can swivel 180 degrees allowing the operator to move around freely, and the slow retraction makes it safe and easy for anyone to handle. If a hose needs to be changed, this can be done easily thanks to its smart design.



#### Hose length on reel

5-17 m

#### Hose material

Braided ester PUR, Antistatic EPDM Rubber

## Reel material

**Plastic** 

# Media

Compressed air


# **Features**

Slow retraction, Hose guiding, Auto-stop. Easy replacement of hose, Soft stop ball.

# **Available options**

High-Visibility hose, Anti-Spark hose, With coupling/nipple

Check with an authorized CEJN distributor for availability and prices. Other connections and sealing material on request. Some part numbers may be subject to minimum order quantities. CEJN reserves the right to make changes without further notification. Thread connections are listed according to ISO Standards. \*Max working pressure at 20°C (68F).



**Air Flow** 

x: Flow, I/min. (CFM)

y: Pressure drop, bar (PSI)