

Product information

74 06 160

High Leverage Diagonal Cutter

DIN ISO 5749 IEC 60900 DIN EN 60900

- For very tough, continuous use
- High cutting performance with minimum effort due to optimum coordination of the cutting edge angle and transmission ratio
- Precision cutting edges additionally induction-hardened (cutting edge hardness approx. 64 HRC), for all sorts of wire including piano wire
- Chrome vanadium heavy-duty steel, forged, multi stage oil-hardened



⚡ 1000 V 



General

Article No.	74 06 160
EAN	4003773040705
Pliers	chrome-plated
Head	chrome-plated
Handles	insulated with multi-component grips, VDE-tested
Weight	215 g
Dimensions	160 x 57 x 19 mm
Standard	DIN ISO 5749 DIN EN 60900 IEC 60900
REACH compliant	no
RohS compliant	no

Technical details

Cutting capacities medium hard wire (diameter)	Ø 3.4 mm
Cutting capacities hard wire (diameter)	Ø 2.5 mm
Cutting capacities piano wire (diameter)	Ø 2.0 mm
VDE tested	yes

Classification

eCl@ss 5.1.4	21040302
ETIM 5.0	EC000165
ETIM 6.0	EC000165
proficl@ss 6.0	AAA949c004
UNSPSC 13.1	27112114

technical change and errors excepted