

Parameters	EU Version
Color	Silver
Capacity	4096Wh
Dimension(L*W*H)	Approx. 694mm*295mm*215mm
Weight(KG)	Approx. 33kg
Display	LED Array
Connection Port	1X Extra Battery Port
	Output: 40V-58.4V=100A Max
Wheels Support	no
Tie rod Support	no
Stack	Horizon or Vertical
Discharge Temperature	-10°C ~ 45°C(14~113°F)
Charge Temperature	0°C ~ 45°C(32~113°F)
Storage Temperature	-10°C ~ 45°C(14~113°F)

