

United Kingdom 3-Pin Plug-in Power Supply 15vdc 7.5watt



The RS Pro Range of Class II 7.5watt AC/DC United Kingdom power supplies provide 7.5 watts of continuous power in a compact fixed wall plug enclosure suitable for use in many general power applications

Features:

- United Kingdom Fixed AC Head
- 3 Year Warranty
- Level VI Efficiency
- CE Approved



Specification	
RS Stock Number	1753295
Input Voltage Range	90-264Vac
Input Frequency Range	50-60Hz
Input Current Rated	0.4A Max
Output Voltage Rating	+15V
Output Current Range	0.5A
Output Min Current	0.01A
Output Connection Type	2.1x5.5x12mm Centre Positive – Straight
Total Output Regulation	+/- 5%
Line and Load Regulation	+/- 5%
Ripple & Noise	150mVp-p
Efficiency	80% Min
Over Voltage Protection	25VDC Maximum
Over Load Protection	2.5A max with auto-recovery function
Operating Temperature	0 to 40°C
Storage Temperature	-20 to +60°C
Operating Humidity	20 to 85%
Storage Humidity	5 to 95%
Hi-Pot	3000VAC 10mA 1min
Leakage Current	0.25mA max
Safety Standard	Meet T-LICENSE(BS EN60950-1)
EMI Standard	Meet CE(EN55022)
MTBF	50K Hours
Size mm max.	79 (L) 50 (W) * 37(H) mm
Weight	110g
Regulator Type	Switched Mode Power Supply