

Product data sheet

Specifications

SQUARE D



Contactor, Definite Purpose, 30A, 2 pole, 110/120 VAC 50/60 Hz coil, open

8910DP32V02

Product availability : Stock - Normally stocked in distribution facility

Price* : 70.88 USD

Main

| | |
|---------------------------|----------------------------|
| Product or Component Type | Definite Purpose Contactor |
| Line Rated Current | 30 A |
| Number of Poles | 2P |
| Pole contact composition | 2 NO |
| Range of Product | DP |

Complementary

| | |
|--------------------------------|--|
| Maximum Horse Power Rating | 2 hp 115 V AC, 1 phase 5 hp 230 V AC, 1 phase |
| Locked rotor rated current | 125 A 460 V AC 100 A 575 V AC 150 A 277 V AC |
| [Ue] rated operational voltage | 600 V AC |
| [Uc] control circuit voltage | 120 V AC 60 Hz 110 V AC 50 Hz |
| Phase | 1 phase |
| Electrical Connection | Binder head Quick connect terminals |

Environment

| | |
|------------------------|----------------------|
| Product Certifications | UL Recognized CSA |
|------------------------|----------------------|

Ordering and shipping details

| | |
|-----------------------|---------------------|
| Category | 21356-8910 DP 32 |
| Discount Schedule | CP1B |
| GTIN | 785901073338 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 9.60 oz (272.155 g) |
| Returnability | Yes |
| Country of origin | CN |

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Packing Units

| | |
|------------------------------|------------------------|
| Unit Type of Package 1 | PCE |
| Package 1 Height | 2.60 in (6.604 cm) |
| Package 1 width | 3.40 in (8.636 cm) |
| Package 1 Length | 2.30 in (5.842 cm) |
| Unit Type of Package 2 | CAR |
| Number of Units in Package 2 | 12 |
| Package 2 Weight | 7.53 lb(US) (3.416 kg) |
| Package 2 Height | 5.80 in (14.732 cm) |
| Package 2 width | 7.10 in (18.034 cm) |
| Package 2 Length | 7.20 in (18.288 cm) |

Offer Sustainability

| | |
|----------------------------|--|
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information. |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|