

har-SAB M8/4/3p PAC 5m PVC w/o LED



Image is for illustration purposes only. Please refer to product description.

Part number	09 07 001 0015 100
Specification	har-SAB M8/4/3p PAC 5m PVC w/o LED
HARTING eCatalogue	https://harting.com/09070010015100

Identification

Series	Circular connectors M8
Element	Distribution boxes
Specification	Pre-assembled master cable

Version

Cable length	5 m
Total number of ports	4
Number of contacts	3

Technical characteristics

Rated current	6 A
Rated voltage	10 V DC 30 V DC
Limiting temperature	-25 ... +85 °C
Degree of protection acc. to IEC 60529	IP67
Number of channels per port	2
Circuit logic	PNP

Material properties

Material (cable)	PVC
RoHS	compliant
ELV status	compliant
China RoHS	e



Pushing Performance
Since 1945

Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Nickel

Commercial data

Packaging size	1
Country of origin	China
European customs tariff number	85444290
GTIN	5713140276635
eCl@ss	27440108 Passive Sensor-Actuator-Interface (with cable)
ETIM	EC002585
UNSPSC 24.0	31251501