



ENGLISH

Datasheet

Stock No: 170-6951

RS Pro Black Braided PVC Cable Sleeve



Image representative of range

Wall thickness:	0.4 mm
Operating temperature:	-30 °C → +105 °C

Approvals

MIL C-20696B, Type 1, Class 2

Product Details

Shielded sleeves for ribbon cables

Electrostatic and RFI shielding sleeves, featuring a 50 µm aluminium foil bonded to vinyl-filled nylon fabric.

These sleeves also feature a tinned copper earth braid along their entire length.

Available for 34-contact flat cable (ref.SHN3BOL) and 60-contact flat cable (ref.SHN304BOL).

Flame and moisture resistant.

Specifications:

Colour	Black
Material	PVC
Braided	Yes
Minimum Operating Temperature	-30°C
Maximum Operating Temperature	+105°C
Shielded	Yes
Wall Thickness	0.4mm