


Technical data

51311

One direction thrust ball bearings



VISUAL (S)



PRODUCT DEFINITION

Brand	NTN
d - Internal diameter	55 mm
D - External diameter	105 mm
T - Thrust bearing height	35 mm
rs - Min fillet radius	1,1 mm
Mass	1,29 kg

PRODUCT PERFORMANCE

Ca - Dynamic axial load rating	119000000 mN
C0a - Static axial load rating	246000000 mN
Cua - Limit axial load rating	11100000 mN
N lim - Oil lubrication limit speed	13800 °/s
N lim - Grease lubrication limit speed	9600 °/s
Tmin - Min operating temperature	233,15 °K
Tmax - Max operating temperature	393,15 °K

ABUTMENT

Da max - Max shoulder diameter OR	75 mm
da min - Min shoulder diameter IR	85 mm

