

FEATURES

- Steel
- IP66
- Simple wall mounting
- All-welded basic body
- High IP index achieved by all-round knife edges against which an expanded PU seal is pressed
- 2.6 mm gauge steel wall brackets
- 1.4 mm wall thickness
- RAL 7032

RS PRO Junction Boxes

RS Stock No.: 122153



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO IP66 Sealed Terminal Boxes

Introducing a range of RS PRO terminal boxes. These boxes are designed for housing DIN rail terminals and accessories. Constructed from 1.5 mm gauge steel and finished in RAL 7032 (grey colour). Inside the lid is a fitted black polyurethane seal gasket that ensures the IP66 rating which offers protection from water, dirt and debris.

General Specifications

Body Material	2.6 mm gauge steel
Base Material	2.6 mm gauge steel
Application	Power Management
Colour	Grey
Lid Colour	Grey
Temperature Range	-20°C to +110°C
Shape	Rectangular
Cover Locking	Screw
RAL Code	RAL 7032

Mechanical Specifications

Length	300 mm
Width	150 mm
Height	120 mm
Internal Dimensions	300 x 150 x 120mm
Wall Thickness	1.4 mm

Protection Category

IP Rating	IP66
------------------	------

Approvals

Declarations	RoHS Certificate of Compliance
--------------	--------------------------------

Similar Products

Stock No.	Brand	Product Name	Material	Dimensions
1444457	RS PRO	Junction Box	Glass Reinforced Polystyrene	220mm x 120mm x 90mm
749-1857	RS PRO	Junction Box	Stainless Steel	150mm x 80mm x 150mm

Connection Diagrams / Assembly Diagrams / Illustrations / Accessories

