

1 B-O11

Combination spanner set

11 pieces

Code	ETIM
6012250	EC011816
EAN	UNSPSC
4010886601228	27-11-17-13
Country of origin	eCl@ss
Germany	21-04-01-05
Customs tariff number	
82041100	



Article description

- Acc. to DIN 3113, Form B, ISO 3318, ISO 7738
- Vanadium steel 31CrV3, chrome-plated
- Carefully forged and professionally machined
- Ring: 10° offset from shaft, with UD profile for gentle transmission of force
- Overloading indicated by deformation
- The offset ring ensures a better grip on deep-seated or inset nuts or bolts
- Top-grade industrial quality for the hardest of continuous use
- Glare-free appearance due to matt chrome
- Jaw: ground precisely to exact nominal size for optimum contact areas
- Slim ribbed open end for added strength guarantees maximum torques

Article parts list

8 9 10 11 12 13 14 15 17 19 22

Article information

Contents (Qty of pieces)	11	Material	Chrome-vanadium steel 31CrV3
Net weight [kg]	1,19 kg	Standard	DIN 3113 - Form B
			ISO 3318
			ISO 7738
Surface	chrome-plated		