


## Features

- NiCr-Ni "K" Type Thermocouples
- Max. operating temperature 400°C
- Protection tube AISI304(DIN1.4301) Stainless Steel
- Sensor type DIN/IEC-584 "K" Type
- Cable type Fiber glass+Fiber glass+Braided
- Tube Diameter 6mm
- Immersion Length 50mm
- Cable Length 1meter

## RS PRO Bayonet Bore "K" Type Thermocouples

RS Stock No: 0350391



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

Standard Bayonet "K" Type Thermocouples Temperature Sensor

Diameter(M): 6mm

Immersion Length(L): 50mm

Cable Length(K): 1m

Applications Fields

- Machinery Manufacturing
- Panel Manufacturing
- Production and Test Equipment
- Food, Chemical, Textile Sectors
- Industrial Control Applications


## General Specifications

Max. Operating Temperature	0 °C / +400 °C
Standard cable types	Fiber glass + fiber glass + braided wire
Sensor type	"K" Type Thermocouples (DIN/IEC-584)
Protection tube material	AISI304 (DIN1.4301) Stainless Steel

## Mechanical Specifications

Diameter (M)	6mm
Immersion Length (L)	50mm
Cable Length (K)	1m

## Electrical Connection



## Thermoelement Connections

