



FIX Adapter Germany CEE7/17 - Switzerland T11 2-pole white, pack of 100 pcs.

Item No.: 14 9562 1
EAN Code: 7611007059002

Description

FIX Adapter Germany CEE7/17 - Switzerland T11, 2-pole, input socket for: Germany (contour plug), output plug: Switzerland (Type 11), input voltage: max. 250V, power: max. 2500W, load: max. 10A, white, pack of 100 pcs.

Specifications

Type	Fixed Adapter
Brand	STEFFEN
Model	CEE 7/17 - Type 11 Wet
Number of Sockets	1
Socket Type	CEE 7/17
Increased Touch Protection	No
Product Colour	White
Rated Current	10 A
Rated Voltage	250 V
Rated Power	2500 W
Plug Type	Type 11
Main Material	Plastic
Halogen-Free	No
UV Resistance	No

Application	Indoor
K2 Suitable for Construction Sites	No
IP Rating	IP20
Operating Temperature Range	-5...+45 °C
Safety Features	Permanently Attached and Non-Removable
Additional Features	Practical Installation Aid Included
Product Height	45 mm
Product Width	45 mm
Product Depth	60 mm
Net Weight	0.032 Kg
Packaging	Open