



Specifications:

Contact rating: 5V DC, 10 mA and 3.6V, 100 mA

Contact resistance: $< 1 \Omega$ Insulation resistance: $> 100 M\Omega$

Dielectric strength: 100 V, 50 Hz for the duration of 1 minute

Operating temperature: -40 °C to +85 °C

Operating force: ≤ 0.4 N


Mechanical life: minimum 100 000 operations
Material: Contacts: copper-alloy, gold-plated

Terminals: brass, silver-plated Case and actuator: HTN, black

Cover: stainless steel

Models: Switching functions


DTS 205 CP-T



DTS 205 C-T off - mom as above, but without posts

DTS 205 CPJ-T off - mom

DTS 205 CJ-T off - mom as above, but without posts



Packing: 2300 pcs/reel