



PRODUCT-DETAILS

CA5-22MRT

CA5-22MRT Auxiliary Contact Block



概要信息	
产品型号	CA5-22MRT
产品ID	1SBN010042R1122
欧洲商品编号(EAN)	3471522364623
目录说明	CA5-22MRT Auxiliary Contact Block
详细描述	CA5-22MRT is a 4-pole front mounted auxiliary contact block equipped with screw terminals for connection with ring tongue ferrules. CA5-..M version offers terminal assortment matching the marking of 3-pole TAL9..40-30-10RT contactors. CA5-22MRT is available with 2 N.O. and 2 N.C. instantaneous contacts for standard industrial environments.

订货信息	
最小起订量	2 piece
海关关税号	85389099

Popular Downloads	
数据手册, 技术资料	1SBC100122C0202_Ch04

说明书和手册	1SBC101011M5501
CAD Dimensional Drawing	2CDC001079B0201

尺寸

产品净宽	43 mm
产品净深	39 mm
产品净高	47 mm
产品净重	0.06 kg

技术参数

辅助触点NO数量	2
辅助触点NC数量	2
额定工作电压	Auxiliary Circuit 690 V
额定频率 (f)	Auxiliary Circuit 50 / 60 Hz
额定工作电流 AC-15 (I _e)	(500 V) 2 A (690 V) 2 A (24 / 127 V) 6 A (220 / 240 V) 4 A (380 / 400 V) 3 A
额定不间断电流 (I _{cw})	for 0.1 s 140 A for 1 s 100 A
额定工作电流 DC-13 (I _e)	(24 V) 6 A / 144 W (48 V) 2.8 A / 134 W (72 V) 1 A / 72 W (110 V) 0.55 A / 60 W (125 V) 0.55 A / 69 W (220 V) 0.30 A / 66 W (250 V) 0.3 / 75 W
额定绝缘电压 (U _i)	acc. to IEC 60947-5-1 690 V acc. to UL/CSA 600 V
防护等级	acc. to IEC 60529, IEC 60947-1, EN 60529 Auxiliary Terminals IP10
端子类型	Ring-Tongue Terminals
适用于	A9 A12 A16 A26 A30 A40 AL9 AL9Z AL12 AL12Z AL16 AL16Z AL26 AL30 AL40 TAL9 TAL12 TAL16 TAL26 TAL30 TAL40

Material Compliance

Conflict Minerals Reporting Template	9AKK108467A5658
--------------------------------------	-----------------

(CMRT)		
REACH Declaration		2CMT2021-006202
RoHS信息		2CMT2021-006277
RoHS状态	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019	
WEEE B2C / B2B		Business To Business
WEEE 类别	5. Small Equipment (No External Dimension More Than 50 cm)	

认证及声明（文件编码）

CB认证	CB_SE_62119A1
CCC认证	CCC_2015010304800518
CQC认证	CQC2015010304800518 CQC2004010305133985
Declaration of Conformity - CCC	2020980304001627 2020980305001185
符合性声明 - CE	1SBD250809U1000
Declaration of Conformity - UKCA	1SBD250826U1000
EAC认证	EAC_RU C-FR ME77 B03391
GOST认证	GOST_POCCFRME77B07175
RINA认证	RINA_ELE172319XG001

包装信息

1级包装单元	2 piece
1级包装宽度	65 mm
1级包装长度	129.5 mm
1级包装高度	43 mm
1级包装 总重	0.12 kg
1级包装 EAN	3471522364623
2级包装单元	200 piece
2级包装 总重	12 kg
3级包装单元	3600 piece

分类

对象分类代码	K
ETIM 7	EC000041 - Auxiliary contact block
ETIM 8	EC000041 - Auxiliary contact block
ETIM 9	EC000041 - Auxiliary contact block
e级	V11.0 : 27371302
UNSPSC	39121522
IDEA 粒度分类代码 (IGCC)	4743 >> Auxiliary contact block

分类

低压产品及系统 → 控制产品 → 接触器 → 模块化接触器

