Gigaset pro

Dimensions

- Handset - 151 x 49 x 26 mm
- Charger - 40 x 81 x 80 mm
- Packaging - 224 x 166 x 60 mm
- Overall weight of the sales packaging approx. 330 g

Contents of the packaging

- Handset
- Battery cover
- 2 AAA Batteries (NiMH)
- Belt clip
- Charger
- Power adapter for charger
- Security leaflet

Environmental conditions

- Operating temperature between +5 to +45° C
- Storage temp between -15 to +60°C
- Relative Humidity between 20% and 75%, non condensating

1) Country, network and base station dependent

It’s your best choice.

Gigaset’s new professional line provides businesses with tailor-made, communication-enhancing phone systems. Discover more! Contact your Gigaset representative or visit **gigasetpro.com**

Issued by Gigaset Communications UK Ltd. All rights reserved. Subject to changes in technology, design and availability.
The product names mentioned in this document are trademarks or registered trademarks of their respective owners. ProDS5650H-UK-1214

Gigaset pro

S650H pro

The new standard in business communication.

The S650H PRO is opimized for everyday use in office environments. The first thing you notice when you hold the S650H PRO is how great it feels in your hand. The volume keys on the side brings absolute convenience while calling where the keypad is just right to dial the right number over and over again. With its high-quality polymer finish, the handset is scratch- and disinfectant resistant. The handset is loaded with Gigaset’s business features enriched with Bluetooth, vibrate and audio profiles. This adapts the phone to fit to your personal needs in specific situations. The micro-usb port prepares the S650H PRO for future software updates to support Gigaset DECT networks. This makes the handset fit perfectly to the N720 DECT IP Multicell and N510 IP single cell System from Gigaset pro. Of course it can also be connected to other GAP compatible base stations in both single- and multicell environments.

Feature highlights:

- Next generation user interface on 1,8”TFT illuminated display
- Side keys for volume adjustment during a call
- Up to 12 hours of talk time. It supports your activities during the day, without re-charging
- Easy installation. Unpack, connect and conduct a call
- Profiles for personal, meeting and noisy environments
- Handsfree talking with brilliant HDSP/CAT-IQ 2.0 sound quality and high maximum volume
- Full compatibility with Gigaset N510 Single and N720 DECT IP Multicell systems
- Modern design with convenient size and proportions
- Searchable local phonebook with up to 500 vCards and corporate phonebook via PBX (XML, LDAP)
- Support of Net provider features via menu
- Vibrating alert
- Silent charger mode during parallel ringing
- Headset connection via Bluetooth® or 2.5 mm jack
- Convenient data exchange via Bluetooth® or micro-USB
- PIN-protected keylock for optimum line security
- Charging via any micro-USB
- Scratch- and disinfectant resistance

green office ENERGY SAVING

MADE IN GERMANY

Multicell with roaming and handover
All features from the Gigaset pro N720 multicell and N510 single-cell portfolio are supported by the S650 handset. Moving in and around the office while calling with the S650 you will experience the convenience and comfort you have come to expect from Gigaset pro; Stay talking, Gigaset pro base stations make sure your connection never falters.

Scratch and disinfectant resistant
The handset is built from a high quality polymer. The handset surface is protected with a unique scratch resistant coating. This ensures the handset will be protected against scratches in daily use . The coating also protects the handset against popular disinfectant influences allowing you to clean the handset responsibly in healthcare environments.

HD Audio makes a call more pleasurable
In handsfree mode, the improved acoustics in Gigaset speaker technology boosts the audio into a higher level. The user experiences an improved sound clarity which brings a new dynamic HD sound quality to the conversation . The standard and your own uploaded ringtones sound even louder and clearer. Using Audio-profiles you adjust the volume level matching your personal business circumstances by pressing one single key.

BECAUSE IT’S YOUR BUSINESS.

S650H pro

The new standard in business communication.

Technical data:

User interface
- Illuminated, graphical 1,8"-TFT Colour display, 128 x 160 Pixel, up to 8 lines and 65.000 colours
- Intuitive, modern user interface with icons, display keys, five way navikey, function keys and side keys

Phonebook and dialling
- Address book with up to 500 vCard entries
- vCard entries: first and last name, three numbers, email, date reminder, VIP melodies and picture caller ID
- PBX-directory access with search (LDAP and XML) [1]
- Public online directory search with auto lookup [1]
- 3 separate calls lists (missed/incoming/outgoing) with 20 entries each with CLIP/CNIP and time/date [1]
- Redialling of last 20 numbers entered
- Short dial keys (soft keys, 9 numeric keys)
- Mute key, key lock and flash key
- Automatic redial function

Receiving calls
- Caller indication displayed via CLIP, picture CLIP and CNIP [1]
- Individual ringer melodies for VIP entries and internal callers
- Anonymous call silencing [1]
- Vibrating alert

Missed calls
- Signalled via display and illuminated message waiting indicator
- List showing up to 20 missed calls with caller indication [1]
- Local missed call list behind 3rd party single and multicell systems with GAP [1]
- Direct dialling of the missed call list

Audio
- HD Audio supporting HDSP™/CAT-IQ 2.0
- Hands free talking with excellent audio quality
- Side keys for easy volume adjustment
- 22 selectable ringer melodies with 5 volume levels and crescendo
- Selectable audio profiles (personal, silent and loud)
- Headset via Bluetooth or 2,5-mm jack

Keypad
- Illuminated and scratch resistant
- Message waiting key with blinking LED
- Separate R-key
- Profile key to apply personal, silent and loud settings directly
- Side keys for volume adjustment
- Keylock (#-key) with PIN protection

Connectivity chart

S650H pro

The new standard in business communication.

Additional Features
- Organiser with calendar and reminder functions
- Email-Reader [1]
- Info services [1]
- Screensaver (picture, slideshow, clock, info service) [1]
- Battery charge also in power off state
- Warning tones when out of the DECT range and visa versa
- Silent charger mode during parallel ringing with other phone registered at the same user

Gigaset QuickSync - Software
- Software free to download for Windows and OSX. Connect via micro-USB or Bluetooth®.
- Synchronize your handset directory with Microsoft Outlook®
- Upload of caller pictures / screensaver pictures
- Upload sounds (ringtones) from computer to handset
- Firmware update
- Computer telephony integration (CTI):
  - Direct dialling of Microsoft Outlook® contacts
  - Display of incoming calls on the computer - both on Windows and OSX

Compatibility
- Optimized and recommended for:
- Gigaset pro Single cell systems - e.g. N510IP PRO
- Gigaset pro Multicell systems - e.g.. N720IP PRO
- GAP compatible DECT base stations (single and multicell systems)

Interfaces
- DECT
- Bluetooth®
- Bluetooth® headset (hands free and headset profile)
- Data exchange and firmware update with Gigaset QuickSync
- vCard exchange with mobile phones
- Micro-USB
- Charging function
- Data exchange and firmware update with Gigaset QuickSync
- 2,5 mm headset connector

DECT range
- Indoor range: up to 50 meters
- Outdoor range: up to 300 meters

Green office
- Up to 60% less energy consumption, thanks to an energy-saving power supply

Operation time
- Up to 12 hours of talk time
- Up to 300 hours of standby time