



ENGLISH

Datasheet

Stock No: 821-419

RS Pro Stainless Steel Extension Spring



Product Details

Stainless Steel Extension Springs

Material to DIN 17224 No. 1 4310 or BS2056 EN58A with a right hand helix
All dimensions conform to DIN 2097 (Grade 2)

Specifications:

Material	Stainless Steel
Free Length	22.1mm
Maximum Extended Length	42.30mm
Outside Diameter	3.2mm
Wire Diameter	0.45mm
Initial Tension	8.91N
Spring Rate	0.407N/mm