



Datasheet

Brass Pneumatic Quick Connect Coupling, G 3/8 Female, Threaded

RS Stock number 667-2018

027 [Quick Release Pneumatic Couplings]

Order No



Interchangeability

RECTUS 27, CEJN 410 TST 410

Temperature Range

-20 C +100 C (-4 F +212 F) Working Pressure

0 - 35 bar (0 - 500 PSI)

Flow Capacity NW - 10 Standard version

Connection

Brass Nickel Plated

Buna (M)

Options

F- Straight Through Flow

K - Chrome Plated

S -Stainless Steel

V - Viton Seal

Material

Coupler Body: Brass Nickel Plated **Back Part: Brass Nickel Plated** Sleeve: Steel Nickel Plated

Valve: Brass

Springs: Stainless Steel

Locking O-Ring: Stainless Steel **Balls: Stainless Steel AISI 420**

Lenght


Dia

Seals: Buna (M)

SW

Plug: Steel Nickel Plated

SUPER FLOW LINE



Couplers and Plugs
Male Thread Coupler

Female Thread
Coupler

R 1/4"	027 EG 13	24	60	28
R 3/8"	027 EG 17	24	60	28
R 1/2"	027 EG 21	24	65	28
R 3/4"	027 EG 26	27	65	28
G 1/4"	027 DG 13	24	57	28
G 3/8"	027 DG 17	24	57	28
G 1/2"	027 DG 21	24	57	28
G 3/4"	027 DG 26	32	61	28





	6 mm 1/4"	027 HG 06	24	75	28
Standart Hose Barb Coupler	8 mm 5/16"	027 HG 08	24	75	28
	9 mm 5/14"	027 HG 09	24	75	28
	10 mm 3/8 "	027 HG 10	24	75	28
	13 mm 1/2"	027 HG 13	24	75	28
	16 mm 5/8 "	027 HG 16	24	75	28
	19 mm 3/4"	027 HG 19	24	75	28
Standart Hose Barb Plug	6 mm 1/4"	027 HU 06		46	
	8 mm 5/16"	027 HU 08		46	
	9 mm 5/14"	027 HU 09		46	
	10 mm 3/8"	027 HU 10		46	
	13 mm 1/2"	027 HU 13		46	
	16 mm 5/8"	027 HU 16		46	
	19 mm 3/4"	027 HU 19		46	
Male Thread Plug	R 1/4"	027 EU 13	17	40	
	R 3/8"	027 EU 17	17	40	
	R 1/2"	027 EU 21	22	46	
	R 1/2 R 3/4"	027 EU 27	27	46	
mare rineau ring	K 5/4	027 20 27	21	40	
and the same of th	G 1/4"	027 DU 13	17	34	
	G 3/8"	027 DU 17	19	24	
	G 1/2"	027 DU 21	24	38	
Female Thread Plug	G 3/4"	027 DU 26	32	42	