



Part Number : [1062835304](#)
Product Description : Quad Small Form-factor Pluggable Plus (QSFP+) Optical Breakout Cable Assembly, 4 TX, 4 RX; 8 Fiber MTP - 8LC Multimode 50/125µm 3.00mm Round Cable Plenum, High Bandwidth (OM3), 10.0m (32.81') (32.81') Length, Aqua Cable
Series Number : 106283
Status : Active
Product Category : Fiber Optic Cable Assemblies



Documents & Resources

Drawings

[1062835304_sd.pdf](#)

Specifications

[885366203-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2020)9139-DC (19 Jan 2021)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Fiber Optic Cable Assemblies
Series	106283
Description	Quad Small Form-factor Pluggable Plus (QSFP+) Optical Breakout Cable Assembly, 4 TX, 4 RX; 8 Fiber MTP - 8LC Multimode 50/125µm 3.00mm Round Cable Plenum, High Bandwidth (OM3), 10.0m (32.81') (32.81') Length, Aqua Cable
Connector to Connector	MTP-to-LC
Mode	Multimode Enhanced
Product Name	MPO,QSFP Plus,QSFP+
UPC	800756706498

Agency

CSA	LR64395
UL	E72548

Physical

Boot Type	N/A
Cable Length	10.0m
Cable Size	3.00mm
Fiber (Core/Cladding)	50/125µm
Net Weight	123.038/g
Single Ended	No

Wire/Cable Type	Round
-----------------	-------

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----