

# Illumination element, 240 V

46-580.1F22

Distribution by  
Rs-online



<https://www.rs-online.eao.com/component/46-58...>

Your product:

---



46-580.1F22

Illumination element, 240 V

*Loading ...*

#### **MOUNTING**

**Mounting type:** Panel mounting

#### **OPERATING-/INDICATION PART**

**Illumination colour:** Orange

#### **ELECTRICAL CHARACTERISTICS**

**Operating voltage:** 240 V AC -20% / +10%

**Protection class:** II, according to EN / IEC 61140

#### **MECHANICAL CHARACTERISTICS**

**Weight:** 0.147 kg

#### **AMBIENT CONDITION**

**IP front protection:** IP44

**IK front protection:** IK07

**Operating temperature:** – 25 °C ... + 65 °C

#### **CERTIFICATE**

**Conformities:** CE

**Standards:** EN 55015, EN 61000-3-2, EN 61000-3-3, EN 61547, IEC EN 60947-1, IEC EN 60947-5-1, IEC EN 62471

## OTHER

|                            |                                                                                    |
|----------------------------|------------------------------------------------------------------------------------|
| <b>Short Description:</b>  | Illumination element, 240 V, Ø 75 mm x 75 mm, Panel mounting, 240 V AC -20% / +10% |
| <b>Titel Accessory:</b>    | Illumination element, 240 V                                                        |
| <b>Dimension:</b>          | Ø 75 mm x 75 mm                                                                    |
| <b>Housing material:</b>   | Plastic                                                                            |
| <b>Product attributes:</b> | For Signal Light Tower                                                             |