



Areas of Application

Universal lockout device for locking out circuit breakers.

Details

- Intuitive design for self-explanatory application
- Holds 1 padlock

Material

- Body : ABS
- Screw: Stainless steel

Dimensions



Body dimensions:

Length: 53 mm

Width: 17 mm

Depth: 35 mm

Temperature Range

- -40°C to +115°C (-40°F to +239°F)

Chemical Resistance

All approved chemicals listed are based on the manufacturer's specified chemical resistance chart for plastic material only.

Chemical	Grade
Mineral lubricants	Conditionally resistant
Aliphatic hydrocarbons	Resistant
Aromatic hydrocarbons	Not resistant
Gasoline	Not resistant
Weak mineral acids	Resistant
Strong mineral acids	Conditionally resistant
Weak organic acids	Resistant
Strong organic acids	Conditionally resistant
Oxidizing acids	Not resistant
Weak bases	Not resistant
Strong bases	Not resistant
Trichloroethylene	Not resistant
Perchloroethylene	Not resistant
Acetone	Not resistant
Alcohols	Conditionally resistant
Hot water (hydrolysis resistance)	Not resistant
UV light and weather	Conditionally resistant

Legal Note

ABUS products are sold with the understanding that the buyers will test them in actual use and determine for themselves their adaptability to their intended uses.