



### Main

Range	Unica
Product or component type	Connector
Accessory / separate part category	Cable accessories
Poles description	1P + N + E
Quantity per set	5

### Complementary

Mounting mode	By screws
Connection position	Direct connection
[In] rated current	16 A
[Ue] rated operational voltage	250 V
Electrical circuit type	Power supply
Electrical connection	Cable 1.5...2.5 mm <sup>2</sup> - rigid or stranded
Cable outer diameter	9 mm
Height	15 mm
Width	24 mm
Depth	54 mm
Material	PA (polyamide)
Colour	White
Product compatibility	Power distribution module

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>