

# Jigsaw LXT®

## DJV184

18V • 0 - 3 000 min<sup>-1</sup>

### Efficient brushless jigsaw with tool-less blade change

An efficient saw with 3 Orbital Settings Plus Straight Cutting and tool-less blade change. Engine speed can be adjusted between 0 and 3 000 min<sup>-1</sup> from a dial to suit the material. A stroke length of 23 mm and cutting capacity of 135 mm in wood and 10 mm in steel.



**LXT** **BL** **SOFT**  
MOTOR NO LOAD

### Technical specifications

|                                                  |                            |
|--------------------------------------------------|----------------------------|
| Voltage LXT                                      | ✓                          |
| Nominal Battery Voltage                          | 18 V                       |
| Brushless Motor                                  | ✓                          |
| Strokes per Minute (SPM)                         | 0 - 3000 min <sup>-1</sup> |
| Length of Stroke                                 | 23 mm                      |
| Max. Cutting Capacity in Wood (90°)              | 135 mm                     |
| Max. Cutting Capacity in Steel (90°)             | 10 mm                      |
| Capacity Aluminium                               | 20 mm                      |
| Orbital Action                                   | ✓                          |
| Tool weight with battery                         | 2,1 - 2,4 kg               |
| Product Dimensions (L x W x H):                  | 259 x 77 x 205 mm          |
| Max. Bevel Range (Left)                          | 0 - 45 °                   |
| Product net weight                               | 1,7 kg                     |
| Vacuum cleaner connection Ø in / out             | 23 / 28 mm                 |
| Vibration Level, Cutting Boards                  | 7,4 m/s <sup>2</sup>       |
| Vibration Uncertainty (K Factor), Cutting Boards | 1,5 m/s <sup>2</sup>       |
| Vibration Level, Cutting Sheet Metal             | 5,1 m/s <sup>2</sup>       |

### User benefits

- Brushless maintenance-free and long-life motor
- LED light illuminates the work site
- Soft no load function automatically reduces the motor speed during idling to suppress the vibration
- Compact and lightweight for reduced operator fatigue
- 3 orbital settings

Link to product - [www.makita.uk.com](http://www.makita.uk.com)



# Related products

## Other

User manual

Parts drawing