

Datasheet

RS Pro Type F - German Schuko 6 Gang Trailing Socket, 2m Cable, 16A, 230 V ac Fused

RS Stock No: **374-193**



Product Details

RS Pro type F - German Schuko trailing socket is an ideal solution for home, office and industrial use. This unprotected socket with 2 m cable, features a CEE 7/7 / Schuko plug and 6 CEE 7/4 (type F Schuko) socket electric sockets in a ruggedized fire retardant ABS plastic case. It has red status indicator to show mains power and fuse OK. This fused socket has a current rating of 16 A and voltage rating of 230 V ac.

Features and Benefits

- Red status indicator to show mains power and fuse OK
- Maximum current rating of 16 A
- Lead length of 2 m (and fitted with a CEE7/7 Schuko type F moulded plug)



ENGLISH

Specifications:

Cord Length	2 m
Corded	Yes
Current Rating	16 A
Fused	Yes
Mains Plug Type	CEE7/7/Schuko
Number of Sockets	6
Power Indicator	Yes
Socket Type	Type F - German Schuko
Surge Protection	No
Voltage Rating	230 V ac
Wired	Yes
Material	ABS Plastic Case
Standards Met	RoHS Compliant