

Electronic housing - ME MAX 22,5 SF G 2-2 KMGY VPE1 - 2201322

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Electronic housing consisting of: Housing shells left and right, front plate, transparent cover, metal foot catch and spring, enclosed housing, 16-pos. (4 x 4 pos.), design: Extra flat, width: 22,5 mm, color: Light gray

The illustration shows the housing versions



Key commercial data

Packing unit	1
GTIN	 4 046356 767002
Custom tariff number	85472000

Technical data

Product type	Complete housing
Approval	UL Recognized
Width	22.5 mm
Height	70.4 mm
Depth	85 mm
No. of pos. for cross connection	5
Type of cross connection	DIN rail bus connector
Functional earth ground contact	Integrated
	without
Color	light gray (7035)
Connection method	Fixed
	Pluggable

Classifications

eCl@ss

eCl@ss 4.0	27180401
eCl@ss 4.1	27180401

Electronic housing - ME MAX 22,5 SF G 2-2 KMGY VPE1 - 2201322

Classifications

eCl@ss

eCl@ss 5.0	27180506
eCl@ss 5.1	27180506
eCl@ss 6.0	27180802
eCl@ss 7.0	27182702
eCl@ss 8.0	27182702

ETIM

ETIM 3.0	EC001031
ETIM 4.0	EC001031
ETIM 5.0	EC001031

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

Approvals

Approvals

Approvals

UL Recognized

Ex Approvals

Approvals submitted

Approval details

UL Recognized 

Accessories

Accessories

Ground contact

Electronic housing - ME MAX 22,5 SF G 2-2 KMGY VPE1 - 2201322

Accessories

Electronic housing - ME FE-CONTACT - 2908294



Functional earth ground contact, for intermediate elements.

Phoenix Contact 2015 © - all rights reserved
<http://www.phoenixcontact.com>