

Datasheet

RS Pro 3A Axial FF Non-Resettable Wire Ended Fuse, 125 V ac/dc

RS Stock No: **764-9488**



Product Details

RS Pro axial non-resettable fuse withstands currents up to 3 A. This wire-ended fuse offers FF speed with a voltage rating of 125 V ac/dc. It has epoxy-coated body for added durability. The very fast acting fuse forms a convenient and reliable solution to a vast array of application requirements.

Features and Benefits

- FF speed fuse
- Non-resettable
- Axial
- Wire-ended

**Specifications:**

Body Diameter	2.65 mm
Body Height	7.1 mm
Body Material	Epoxy Coated
Breaking Capacity (at Maximum Voltage Rating)	300 A at 125 V dc, 50 A at 125 V ac
Current Rating	3 A
Fuse Speed	FF
Lead Orientation	Axial
Maximum Operating Temperature	+125°C
Minimum Operating Temperature	-55°C
Voltage Rating	125 V ac/dc
Voltage Rating	125 V ac/dc
Wire Diameter	0.65 mm
Wire Length	28 mm
Fuse Type	Very Fast Acting
Nominal Resistance	0.024 Ω
Standards Met	TUV, PSE, RoHS