



SAPPHIRE Dynamic

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878
Issue date: 12/02/2025 Version: 1.0

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product form : Mixture
Trade name : SAPPHIRE Dynamic
UFI : E7V0-A0GA-3007-3KQN
Product code : 12351,12353,12357

1.2. Relevant identified uses of the substance or mixture and uses advised against

Relevant identified uses

Main use category : Industrial use, Professional use
Industrial/Professional use spec : Industrial
For professional use only
Use of the substance/mixture : Lubricants, Greases and Release Products

1.3. Details of the supplier of the safety data sheet

ROCOL a division of ITW Ltd
Rocol House
Wakefield Rd, Swillington
LS26 8BS Leeds, West Yorkshire
United Kingdom
T +44 (0)113 232 2600
customer.service@rocol.com, www.rocol.com

1.4. Emergency telephone number

Emergency number : +44 (0)113 232 2600

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No. 1272/2008 [CLP]

Serious eye damage/eye irritation, Category 2 H319
Full text of H- and EUH-statements: see section 16

Adverse physicochemical, human health and environmental effects

No additional information available

2.2. Label elements

Labelling according to Regulation (EC) No. 1272/2008 [CLP]

Hazard pictograms (CLP) :



GHS07

Signal word (CLP) : Warning
Hazard statements (CLP) : H319 - Causes serious eye irritation.
Precautionary statements (CLP) : P264 - Wash hands, forearms and face thoroughly after handling.
P280 - Wear protective clothing, eye protection, face protection.
P305+P351+P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P337+P313 - If eye irritation persists: Get medical advice/attention.

SAPPHIRE Dynamic

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

2.3. Other hazards

Contains no PBT and/or vPvB substances $\geq 0.1\%$ assessed in accordance with REACH Annex XIII

The mixture does not contain substance(s) included in the list established in accordance with Article 59(1) of REACH for having endocrine disrupting properties, or substance(s) are not identified as having endocrine disrupting properties in accordance with the criteria set out in Commission Delegated Regulation (EU) 2017/2100 or Commission Regulation (EU) 2018/605 at a concentration equal to or greater than 0,1 %

SECTION 3: Composition/information on ingredients

3.2. Mixtures

Name	Product identifier	%	Classification according to Regulation (EC) No. 1272/2008 [CLP]
CALCIUM BENZENE DODECYL SULPHONATE	CAS-No.: 1335202-81-7 EC-No.: 932-231-6 REACH-no: 01-2119560592-37	2.4 – 15	Skin Irrit. 2, H315 Eye Dam. 1, H318 Aquatic Chronic 3, H412

Full text of H- and EUH-statements: see section 16

SECTION 4: First aid measures

4.1. Description of first aid measures

First-aid measures general	: Never give anything by mouth to an unconscious person. If you feel unwell, seek medical advice (show the label where possible).
First-aid measures after inhalation	: Allow affected person to breathe fresh air. Allow the victim to rest.
First-aid measures after skin contact	: Remove affected clothing and wash all exposed skin area with mild soap and water, followed by warm water rinse.
First-aid measures after eye contact	: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.
First-aid measures after ingestion	: Rinse mouth. Do NOT induce vomiting. Obtain emergency medical attention.

4.2. Most important symptoms and effects, both acute and delayed

Symptoms/effects after eye contact	: Causes serious eye irritation.
------------------------------------	----------------------------------

4.3. Indication of any immediate medical attention and special treatment needed

No additional information available

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media	: Foam. Dry powder. Carbon dioxide. Water spray. Sand.
Unsuitable extinguishing media	: Do not use a heavy water stream.

5.2. Special hazards arising from the substance or mixture

No additional information available

5.3. Advice for firefighters

Firefighting instructions	: Use water spray or fog for cooling exposed containers. Exercise caution when fighting any chemical fire. Prevent fire fighting water from entering the environment.
Protection during firefighting	: Do not enter fire area without proper protective equipment, including respiratory protection.

SAPPHIRE Dynamic

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

For non-emergency personnel

Emergency procedures : Evacuate unnecessary personnel.

For emergency responders

Protective equipment : Equip cleanup crew with proper protection.

Emergency procedures : Ventilate area.

6.2. Environmental precautions

Prevent entry to sewers and public waters. Notify authorities if liquid enters sewers or public waters.

6.3. Methods and material for containment and cleaning up

Methods for cleaning up : On land, sweep or shovel into suitable containers. Minimise generation of dust. Store away from other materials.

6.4. Reference to other sections

See Section 8. Exposure controls and personal protection.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Precautions for safe handling : Wash hands and other exposed areas with mild soap and water before eating, drinking or smoking and when leaving work. Provide good ventilation in process area to prevent formation of vapour.

Hygiene measures : Wash hands, forearms and face thoroughly after handling.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions : Keep only in the original container in a cool, well ventilated place away from : Keep container closed when not in use.

Incompatible products : Strong bases. Strong acids.

Incompatible materials : Sources of ignition. Direct sunlight.

7.3. Specific end use(s)

No additional information available

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

No additional information available

8.2. Exposure controls

Personal protection equipment

Personal protective equipment:

Avoid all unnecessary exposure.

Personal protective equipment symbol(s):



Eye and face protection

Eye protection:

Chemical goggles or safety glasses

SAPPHIRE Dynamic

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

Skin protection

Hand protection:

Wear protective gloves.

Respiratory protection

Respiratory protection:

Wear appropriate mask

Environmental exposure controls

Other information:

Do not eat, drink or smoke during use.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state	: Solid
Colour	: Beige, brown.
Appearance	: Paste.
Odour	: characteristic.
Odour threshold	: Not available
Melting point	: > 280 °C
Freezing point	: Not available
Boiling point	: Not available
Flammability	: Non flammable.
Lower explosion limit	: Not applicable
Upper explosion limit	: Not applicable
Flash point	: > 200
Auto-ignition temperature	: > 320
Decomposition temperature	: Not available
pH	: Not available
pH solution	: Not available
Viscosity, kinematic	: > 20.5 mm²/s
Solubility	: immiscible.
Partition coefficient n-octanol/water (Log Kow)	: Not available
Vapour pressure	: Not available
Vapour pressure at 50°C	: Not available
Density	: Not available
Relative density	: 0.9 – 1.1
Relative vapour density at 20°C	: Not applicable
Particle size	: Not available

9.2. Other information

No additional information available

SECTION 10: Stability and reactivity

10.1. Reactivity

No additional information available

10.2. Chemical stability

Not established.

10.3. Possibility of hazardous reactions

Not established.

10.4. Conditions to avoid

Direct sunlight. Extremely high or low temperatures.

SAPPHIRE Dynamic

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

10.5. Incompatible materials

Strong acids. Strong bases.

10.6. Hazardous decomposition products

fume. Carbon monoxide. Carbon dioxide.

SECTION 11: Toxicological information

11.1. Information on hazard classes as defined in Regulation (EC) No 1272/2008

Acute toxicity (oral) : Not classified
Acute toxicity (dermal) : Not classified
Acute toxicity (inhalation) : Not classified

CALCIUM BENZENE DODECYL SULPHONATE (1335202-81-7)

LD50 oral rat	4445 mg/kg bodyweight Animal: rat, Animal sex: female, Guideline: other., 95% CL: 3913 - 5051
LD50 dermal rat	> 2000 mg/kg bodyweight Animal: rat, Guideline: OECD Guideline 402 (Acute Dermal Toxicity)

Skin corrosion/irritation : Not classified
Additional information : Based on available data, the classification criteria are not met
Serious eye damage/irritation : Causes serious eye irritation.
Respiratory or skin sensitisation : Not classified
Additional information : Based on available data, the classification criteria are not met
Germ cell mutagenicity : Not classified
Additional information : Based on available data, the classification criteria are not met
Carcinogenicity : Not classified
Additional information : Based on available data, the classification criteria are not met
Reproductive toxicity : Not classified
Additional information : Based on available data, the classification criteria are not met
STOT-single exposure : Not classified
Additional information : Based on available data, the classification criteria are not met
STOT-repeated exposure : Not classified
Additional information : Based on available data, the classification criteria are not met
Aspiration hazard : Not classified
Additional information : Based on available data, the classification criteria are not met

SAPPHIRE Dynamic

Viscosity, kinematic	> 20.5 mm²/s
----------------------	--------------

11.2. Information on other hazards

Other information

Potential adverse human health effects and symptoms : Based on available data, the classification criteria are not met

SECTION 12: Ecological information

12.1. Toxicity

Hazardous to the aquatic environment, short-term (acute) : Not classified
Hazardous to the aquatic environment, long-term (chronic) : Not classified

CALCIUM BENZENE DODECYL SULPHONATE (1335202-81-7)

LC50 - Fish [1]	1.67 mg/l Test organisms (species): Lepomis macrochirus
-----------------	---

SAPPHIRE Dynamic

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

CALCIUM BENZENE DODECYL SULPHONATE (1335202-81-7)

EC50 - Crustacea [1]	2.9 mg/l Test organisms (species): Daphnia magna
EC50 96h - Algae [1]	29 mg/l Test organisms (species): Raphidocelis subcapitata (previous names: Pseudokirchneriella subcapitata, Selenastrum capricornutum)
NOEC (chronic)	1.18 mg/l Test organisms (species): Daphnia magna Duration: '21 d'
NOEC chronic fish	0.23 mg/l Test organisms (species): Oncorhynchus mykiss (previous name: Salmo gairdneri) Duration: '72 d'

12.2. Persistence and degradability

SAPPHIRE Dynamic

Persistence and degradability	Not established.
-------------------------------	------------------

CALCIUM BENZENE DODECYL SULPHONATE (1335202-81-7)

Persistence and degradability	Rapidly degradable
-------------------------------	--------------------

12.3. Bioaccumulative potential

SAPPHIRE Dynamic

Bioaccumulative potential	Not established.
---------------------------	------------------

12.4. Mobility in soil

No additional information available

12.5. Results of PBT and vPvB assessment

No additional information available

12.6. Endocrine disrupting properties

No additional information available

12.7. Other adverse effects

SAPPHIRE Dynamic

Other information	Avoid release to the environment.
-------------------	-----------------------------------

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Product/Packaging disposal recommendations : Dispose in a safe manner in accordance with local/national regulations.
Ecological waste information : Avoid release to the environment.

SECTION 14: Transport information

In accordance with ADR / IMDG / IATA / ADN / RID

ADR	IMDG	IATA	ADN	RID
14.1. UN number or ID number				
Not regulated for transport				
14.2. UN proper shipping name				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated

SAPPHIRE Dynamic

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

ADR	IMDG	IATA	ADN	RID
14.3. Transport hazard class(es)				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
14.4. Packing group				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
14.5. Environmental hazards				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
No supplementary information available				

14.6. Special precautions for user

Overland transport

Not regulated

Transport by sea

Not regulated

Air transport

Not regulated

Inland waterway transport

Not regulated

Rail transport

Not regulated

14.7. Maritime transport in bulk according to IMO instruments

Not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

EU-Regulations

REACH Annex XVII (Restriction List)

Contains no substance(s) listed on REACH Annex XVII (Restriction Conditions)

REACH Annex XIV (Authorisation List)

Contains no substance(s) listed on REACH Annex XIV (Authorisation List)

REACH Candidate List (SVHC)

Contains no substance(s) listed on the REACH Candidate List

PIC Regulation (Prior Informed Consent)

Contains no substance(s) listed on the PIC list (Regulation EU 649/2012 concerning the export and import of hazardous chemicals)

POP Regulation (Persistent Organic Pollutants)

Contains no substance(s) listed on the POP list (Regulation EU 2019/1021 on persistent organic pollutants)

Ozone Regulation (2024/590)

Contains no substance(s) listed on the Ozone Depletion list (Regulation EU 2024/590 on substances that deplete the ozone layer)

Council Regulation (EC) for the control of dual-use items

Contains no substance subject to the COUNCIL REGULATION (EC) for the control of dual-use items

Explosives Precursors Regulation (2019/1148)

Contains no substance(s) listed on the Explosives Precursors list (Regulation EU 2019/1148 on the marketing and use of explosives precursors)

SAPPHIRE Dynamic

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

Drug Precursors Regulation (273/2004)

Contains no substance(s) listed on the Drug Precursors list (Regulation EC 273/2004 on the manufacture and the placing on market of certain substances used in the illicit manufacture of narcotic drugs and psychotropic substances)

15.2. Chemical safety assessment

No chemical safety assessment has been carried out

SECTION 16: Other information

Data sources : REGULATION (EC) No 1272/2008 OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL of 16 December 2008 on classification, labelling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and amending Regulation (EC) No 1907/2006.

Other information : None.

Full text of H- and EUH-statements:

Aquatic Chronic 3	Hazardous to the aquatic environment – Chronic Hazard, Category 3
Eye Dam. 1	Serious eye damage/eye irritation, Category 1
Skin Irrit. 2	Skin corrosion/irritation, Category 2
H315	Causes skin irritation.
H318	Causes serious eye damage.
H319	Causes serious eye irritation.
H412	Harmful to aquatic life with long lasting effects.

Safety Data Sheet (SDS), EU

This information is based on our current knowledge using information from our raw material suppliers and describes the product for health, safety and environmental purposes only. It should therefore not be interpreted as guaranteeing any specific property of the product. This information does not exempt the user from checking the product and in no way engages our responsibility as to the use for which it is intended.