

**32 30**

## Socket 3/4"

hexagon UD profile

|                       |                    |
|-----------------------|--------------------|
| Code                  | ETIM               |
| <b>6270700</b>        | <b>EC002203</b>    |
| EAN                   | UNSPSC             |
| <b>4010886627075</b>  | <b>27-11-17-04</b> |
| Country of origin     | eCl@ss             |
| <b>Germany</b>        | <b>21-04-02-18</b> |
| Customs tariff number |                    |
| <b>82042000</b>       |                    |



## Article description

- Acc. to DIN 3124, ISO 2725-1
- Square drive as per DIN 3120 - D 20, ISO 1174, with locking pin
- Manually operated, with non-slip cross knurling
- Vanadium steel 31CrV3, matt chromium-plated

## Article information

|  |                                     |                                      |   |
|--|-------------------------------------|--------------------------------------|---|
| Contents (Qty of pieces)               | <b>1</b>                            | Drive connector square female [inch] | <b>3/4"</b>   |
| Net weight [kg]                        | <b>0,331 kg</b>                     | Standard                             | <b>DIN 3124<br/>ISO 2725-1<br/>DIN 3120 - D 20<br/>ISO 1174</b> |
| Total length [mm]                      | <b>58 mm</b>                        | Width across flats 1 [mm]            | <b>30</b>   |
| Total width [mm]                       | <b>43 mm</b>                        | Backup                               | <b>Locking pin</b>  |
| Total height [mm]                      | <b>43 mm</b>                        | Insert-Ø 1                           | <b>43,3 mm</b>  |
| Surface                                | <b>Matt chrome-plated</b>           | Working length                       | <b>57,5 mm</b>  |
| Material                               | <b>Chrome-vanadium steel 31CrV3</b> | Insert-Ø 2                           | <b>38,0 mm</b>  |
| Drive connector square female (metric) | <b>20,0 mm</b>                      | Operating depth                      | <b>26,0 mm</b>  |