



DW03050

LASER DISTANCE METER - 50M

Selling Proposition

- Laser distance measurer (LDM) manufactured to withstand the inevitable job site drops and falls on the Job site
- It has a range of up to 50m and an accuracy of +/- 1,5mm
- Common end-user functions : linear meter readings, surface and volume calculations. It will add or subtract readings and calculate distance in Metric and Imperial.
- The user can select the unit to continually measure which allows layout applications.
- Pythagoras indirect height function will allow to measure distances even when point A and/or point B isn't accessible for linear measurement
- Unit stores last 5 measurements

Standard Equipment

- 2 x 1.5v dc LR03 (AAA-size) batteries

Warranty Specifications

- 30 Tage-Geld-zurück-Garantie
- 1 Year Free Service Contract
- 1 Year Warranty

Specifications	
Laser class	Class 2
Levelling Accuracy	+/- 1,5mm/m
Self-levelling range	N/A °
Number of beams	1
Direction of beams	N/A
Indoor Visibility Range	50m m
Power Source	2 x 1.5v dc LR03 (AAA-size) batteries
Tripod connection	N/A