

Features

- 5 mm pitch
- Voltage Rating: 300V
- Current Rating: 15A
- Low Mating Force
- 2 WAY SCREWLESS 15A TERMINAL

RS PRO 5MM PITCH 2 WAY SCREWLESS 15A TERMINAL

RS Stock No.: 0631105



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

- Vertical mount PCB screwless terminal blocks with a 5.0mm pitch, levers and a 300V 15A electrical rating. These 5.0mm PCB terminal blocks have screwless cage clamp terminals that accept a wire size of 28 to 12 AWG and white PA66 housings.
- Standard accepts wire 28-12AWG 2.5 mm²

General Specifications

Number of Contacts	2
Number of Rows	1
Pitch	5mm
Mounting Type	Through Hole
Type	PCB Terminal Block
Body Orientation	Straight
Number of P	2
Gender	Male
Clamping	Stainless steel
Contact Material	Brass
Contact Plating	Tin plated
Housing	PA66(UL94V-0)
Colour	Grey

Electrical Specifications

Voltage Rating	300V
Current Rating	15A
Insulation Resistance	500M ohm min
Withstanding Voltage	2000V AC/minute

Mechanical Specifications

Mounting Type	Through Hole
Pitch	5.0 mm
Pin size	Please see below drawings
Pin height	3.5mm

Operation Environment Specifications

Operating Temperature	-40°C to 105°C
-----------------------	----------------

Approvals

Compliance/Certifications	RoHS Compliant, CE
Declarations	Reach

Spec Drawings

