

DIFLEX PVC HOSE - COIL



FOOD INDUSTRY

ID/OD (mm)	Coil (m)	Bend radius (mm)	Max operating pressure (bar)	Colour	Part Numbers
6 x 12	50	36	15	Blue	DIFLEX 6
8 x 14	50	54	15	Blue	DIFLEX 8
8 x 14	50	54	15	Red	DIFLEX 8RG
8 x 14	25	54	15	Blue	DIFLEX 8C25
9 x 15	50	66	15	Blue	DIFLEX 9
10 x 16	50	74	15	Blue	DIFLEX 10
10 x 16	50	74	15	Red	DIFLEX 10RG
10 x 16	25	74	15	Blue	DIFLEX 10C25
12 x 19	50	90	15	Blue	DIFLEX 12
12 x 19	50	90	15	Red	DIFLEX 12RG
13 x 20	50	101	15	Blue	DIFLEX 13
13 x 20	50	101	15	Red	DIFLEX 13RG
16 x 22	25	145	15	Blue	DIFLEX 16
19 x 26	25	174	15	Blue	DIFLEX 19
25 x 33	25	260	15	Blue	DIFLEX 25
32 x 42	25	320	12	Clear	DIFLEX 32
38 x 48	25	420	11	Clear	DIFLEX 38
50 x 64	25	600	8	Clear	DIFLEX 50

Temperature: -15°C to +60°C

AIRCA RUBBER HOSE - COIL



ID/OD (mm)	Coil (m)	Bend radius (mm)	Max operating pressure (bar)	Colour	Part Numbers
6 x 13	40	18	20	Blue - Black	AIRCA 6
8 x 15	40	25	20	Blue - Black	AIRCA 8
8 x 15	20	25	20	Blue - Black	AIRCA 8C20
10 x 18	40	35	20	Blue - Black	AIRCA 10
13 x 22	40	60	20	Blue - Black	AIRCA 13
16 x 25	40	70	15	Blue - Black	AIRCA 16
19 x 28	40	80	15	Blue - Black	AIRCA 19
25 x 34	40	100	15	Blue - Black	AIRCA 25

Rubber hose with alternating blue and black stripes

Outer sheath made from smooth black EPDM

Inner lining made from smooth black SBR, reinforced with a synthetic fabric braid

Lubricated air supply for pneumatic tools

Temperature: -40°C to +70°C