

## FEATURES

- **Nylon Material:** Provides durability and resistance to wear and tear
- **UV Resistant:** Suitable for outdoor use, resisting degradation from sunlight
- **Tensile Strength of 34 kg:** Ensures strong and reliable cable bundling
- **Maximum Bundle Diameter of 74 mm:** Accommodates a wide range of cable sizes
- **Operating Temperature up to 85 °C:** Suitable for use in high-temperature environments
- **UL 94 V-2 Fire Behaviour:** Offers flame retardant properties for added safety

## RS PRO Nylon Cable Tie, 300mm Non-Releaseable

RS Stock No: 656-059



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

### Product Description

These RS PRO nylon cable ties are designed for securing and organising cables efficiently. With a length of 300 mm, they are ideal for bundling cables in various industrial and commercial settings. The non-releasable design ensures a secure hold, making them perfect for permanent installations.

### General Specifications

Colour	Black
Product Type	Cable Tie
Sub Type	Non-Releasable
Tensile Strength	34 kg

### Protection Category

Fire Behaviour	UL 94 V-2
UV Resistant	Yes

### Mechanical Specifications

Length	300 mm
Material	Nylon
Maximum Bundle Diameter	74 mm
Width	4.8 mm

### Operation Environment Specifications

Maximum Operating Temperature	85 °C
-------------------------------	-------

### Approvals

Standards/Approvals	ABS 15-TA1338482-PDA, cULus E97527, RoHS, UL94V-2
---------------------	---