

Slide Compound Mitre Saw LXT®

DLS211

18V x 2 • 305 mm • 4 400 min⁻¹

Battery powered saw, but the power and speed of an electric machine!

Battery powered 2 x 18V mitre saw for heavy duty use. Equipped with AWS vacuum remote start function (Bluetooth). Heavy cutting height 107 mm and width 382 mm. Cutting speed and power of an electric machine in a cordless machine.



Technical specifications

Brushless Motor	✓
Max. kerf thickness of the saw blade	3,2 mm
Capacity 90°	107 x 363 / 92 x 382 mm
Nominal Battery Voltage	2 x 18 V
Voltage LXT	✓
No load speed	4400 min ⁻¹
Capacity 45°	107 x 255 / 92 x 268 mm
Capacity 45° left	71 x 363 / 61 x 382 mm
Bevel capacity right 45°	54 x 363 / 44 x 382 mm
Max. Bevel Range (Left)	48 / 48 °
Max. Mitre Range (Left)	60 / 60 °
Blade Diameter	305 mm
Bore Size (Arbor Diameter)	30 mm
Sound Power Level (L _{WA})	103 dB(A)

User benefits

- Brushless maintenance-free and long-life motor
- Auto-start Wireless System (AWS) connects to compatible vacuum cleaners with Bluetooth
- ADT (Automatic torque Drive Technology) adjusts speed and torque during operation for optimum performance
- Mitre 0 - 60°, left and right. Positive Mitre stops at; 0°, 15°, 22.5°, 31.6°, 45° and 60° left or right
- Battery protection system automatically shuts off power when the battery level is low
- Large turn base supports workpiece securely for increased stability
- Oversized trigger switch for better fit, added comfort and easier operation

Link to product - www.makita.uk.com



Related products

■ Optional AC

122470-4

Horizontal Vice Assembly



■ Other

User manual

Parts drawing