



PRODUCT-DETAILS**BVNV-P112****COND FTNG STR PG11 NW12 IP68 BLK**

General Information

Extended Product Type:	BVNV-P112
Product ID:	7TAA292150R0302
EAN:	7630030231391
Catalog Description:	COND FTNG STR PG11 NW12 IP68 BLK
Long Description:	VN Straight Connector, PG Thread for IP68 Static Conduit - Thread PG 11, Fits to Conduit Size NW/Metric 12/16, Color Black
Display Name:	BVNV-P112

Additional Information

Product Main Type:	PMA Flexible Cable Protection
Application:	Use In Railway Vehicle and Heavy Machine Construction
Product Type:	Fittings for Nylon Flexible Conduits

Ordering

EAN:	7630030231391
UPC:	786209952608

Technical

Number of Batteries:	0
Color:	Black
Material:	Polyamide 6
Size:	NW12 , PG11 Thread

Environmental

WEEE Category:	Product Not in WEEE Scope
-----------------------	---------------------------

Container Information

Package Level 1 Units:	50 EA
Package Level 1 EAN:	7630030231391
Package Level 1 Height:	0 mm 0 in
Package Level 1 Depth / Length:	0 mm 0 in
Package Level 1 Width:	0 mm 0 in

Certificates and Declarations

Data Sheet, Technical Information:	BVNV-P112
Instructions and Manuals:	BVNV-P112
Declaration of Conformity - CE:	9AKK107680A0674

External Classifications and Standards

ETIM 8:	EC001176 - Screw connection for corrugated plastic hose
ETIM 9:	EC001176 - Screw connection for corrugated plastic hose
UNSPSC:	39121311

Categories

Products > Low Voltage Products and Systems > Installation Products > Cable Protection, Explosion Proof and Lighting > Flexible Cable Protection Systems

