

ESD SMD tweezers set 11 pcs with holder TWEEZ

Art.-No.	5-170
Description	ESD SMD tweezers set 11 pcs with holder TWEEZ
Application	assembly tweezers, SMD/THT, precision tweezers
Specification	Dimensions see data sheets individual articles (pictogram)
Material	stainless steel
Surface/Coating	matt finish
Features	stainless, antimagnetic, acid-resistant, dissipative
Surface resistance	/
Total length	Dimensions holder 125 × 40 × 50 mm
Weight	weight 290 g

Application and technical data

The stainless steel precision tweezers are rustproof, matt polished, anti-magnetic, acid-resistant and with ESD coating. High quality cutting tweezers made of carbon steel. Best suited for soft copper wire, gold and silver wire up to Ø 0.25 mm. The cutting edges are particularly sharp and hard for oblique cutting. The conductive plastic tweezers are made of technical high-performance plastic (Vestamid PA12 L-Ployamid), clean room compatible, glass fiber reinforced, resistant to acids and can be used up to 175° C.

The tweezers and the tweezer holder are EPA suitable, for working in electrostatically protected areas (ESD workplace/ESD protection zone). Of course, all other suitable ESD tools can also be stored in it. For standing or hanging with long holes suitable for tool walls pegboards (Küpper tool wall, Tegometall, element system). Above 11 holes with the dimensions approx. 11 × 9 mm, opposite below 11 fixing oblong holes in the bottom with the dimensions approx. 10 × 4 mm, made of sturdy 1.7 mm sheet steel.

Parts list

ESD SMD precision tweezers set consisting of:

- 5-170-0 ESD tweezers holder TWEEZ steel light grey RAL 7035 dissipative
- 5-048-13 ESD SMD tweezers 110 mm form 5 stainless steel, very pointed
- 5-055-13 ESD SMD tweezers 120 mm form 7a stainless steel 40° dissipative
- 5-059-13 ESD SMD tweezers 120 mm form 2a stainless steel, dissipative
- 5-066-13 ESD SMD tweezers 120 mm form 8b stainless steel 30° dissipative
- 5-067-13 ESD SMD tweezers 120 mm form 12 stainless steel 45° dissipative
- 5-068-13 ESD tweezers 120 mm form 13 stainless steel 45° dissipative
- 5-069-13 ESD SMD tweezers 115 mm form 5abb-Z stainless steel 30° serrated, dissipative
- 5-079-13 ESD cutting tweezers (slanted) 115 mm Form 15 AGW, dissipative
- 5-191 ESD plastic precision tweezers 120 mm Form 2a tip 2 mm wide conductive
- 5-192 ESD plastic precision tweezers 120 mm Form F tip 3 mm wide conductive
- 5-194 ESD plastic precision tweezers 120 mm Form 6 hook tip conductive

