

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300580025](#)
Status: **Active**
Overview: Brad Industrial Ethernet Solutions
Description: Ultra-Lock (M12) D-Coded to RJ-45 Adapter, Straight to Straight, 4-Pole Female to RJ45 Male, Unshielded PVC, 1.0m (3.28') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E200650

General

Product Family Industrial Receptacles
 Series [130058](#)
 IP Rating IP67
 Overview [Brad Industrial Ethernet Solutions](#)
 Product Name RJ45, Ultra-Lock (M12)
 Type Double Ended
 UPC 78678802441

Physical

Coupling Type Push to Lock
 Gender Female-Male
 Keyway D-coded
 Length 1.0m
 Material - Component Nickel-plated Brass
 Mounting Thread Size PG9
 Net Weight 150.000/g
 Orientation Straight
 Panel Mount Back
 Poles 4
 Temperature Range - Operating -25° to +80°C
 Wire Size AWG 24
 Wire/Cable Type Unshielded PVC

Electrical

Current - Maximum per Contact 0.5A
 Voltage - Maximum 250V AC/DC

Material Info

Engineering Number ERWPAB3002M010

Reference - Drawing Numbers

Sales Drawing SD-130054-002-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - D(2020)4578-DC (25 June 2020)

Lead

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

ZZCERT_CE -

Declaration of

Conformity

China RoHS

50 Image

Not Relevant

Not Contained

CER_4000380967_00_000.pdf

Search Parts in this Series

[130058 Series](#)