


THIS INFORMATION IS CONFIDENTIAL AND IS DISCLOSED TO YOU ON CONDITION THAT NO FURTHER DISCLOSURE IS MADE BY YOU TO OTHER THAN THE PERSONNEL WITHOUT WRITTEN AUTHORIZATION FROM TE INCORPORATED, HARRISBURG, PA.

WAS 78-9833



SEL. GOLD PLATED	CuSn	CONTACT - PIN	HOUSING 926 207
COLOR: GREEN	PBTP	NAME	
FINISH	MATERIAL		

### AMP MODU II PIN HEADER

PIN N) 1	9-927 949-00	1-926 807-30	6-927 949-10	7-927 949-5	8-927 949-7	1-926 809-40
1	.100	.254	826 634-1	826 663-1	826 664-1	826 665-1
2	200	508	-2	-2	-2	-2
3	300	762	-3	-3	-3	-3
4	400	1016	-4	-4	-4	-4
5	500	1270	-5	-5	-5	-5
6	600	1524	-6	-6	-6	-6
7	700	1778	-7	-7	-7	-7
8	800	2032	-8	-8	-8	-8
9	900	2286	-9	-9	-9	-9
10	1000	2540	-0	-0	-0	-0
11	1100	2794	-1	-1	-1	-1
12	1200	3048	-2	-2	-2	-2
13	1300	3302	-3	-3	-3	-3
14	1400	3556	-4	-4	-4	-4
15	1500	3810	-5	-5	-5	-5
16	1600	4064	-6	-6	-6	-6
17	1700	4318	-7	-7	-7	-7
18	1800	4572	-8	-8	-8	-8
19	1900	4826	-9	-9	-9	-9
20	2000	5080	-0	-0	-0	-0
21	2100	5334	-1	-1	-1	-1
22	2200	5588	-2	-2	-2	-2
23	2300	5842	-3	-3	-3	-3
24	2400	6096	-4	-4	-4	-4
25	2500	6350	-5	-5	-5	-5
26	2600	6604	-6	-6	-6	-6
27	2700	6858	-7	-7	-7	-7
28	2800	7112	-8	-8	-8	-8
29	2900	7366	-9	-9	-9	-9
30	3000	7620	-0	-0	-0	-0
31	3100	7874	-1	-1	-1	-1
32	3200	8128	-2	-2	-2	-2
33	3300	8382	-3	-3	-3	-3
34	3400	8636	-4	-4	-4	-4
35	3500	8890	-5	-5	-5	-5
36	3600	9144	-6	-6	-6	-6
37	3700	9398	-7	-7	-7	-7
38	3800	9652	-8	-8	-8	-8
39	3900	9906	-9	-9	-9	-9
40	4000	10160	-0	-0	-0	-0
41	4100	10414	-1	-1	-1	-1
42	4200	10668	-2	-2	-2	-2
43	4300	10922	-3	-3	-3	-3
44	4400	11176	-4	-4	-4	-4
45	4500	11430	-5	-5	-5	-5
46	4600	11684	-6	-6	-6	-6
47	4700	11938	-7	-7	-7	-7
48	4800	12192	-8	-8	-8	-8
49	4900	12446	-9	-9	-9	-9
50	5000	12700	-0	-0	-0	-0

NOTE

⚠ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

⚠ OBSOLETE

PRELIMINARY ISSUE  
NOT RELEASED  
FOR PRODUKTION

NAME: H# DATE: 10.1.79

LOC  
R1  
DIST

DRAWING VALID FROM  
ZEICHNUNG GÜLTIG AB

H2	ECR-10-025774	HMR	13JUN11
H1	ECO-10-000445	AEG	12JAN10
PI	LTR	REVISION RECORD	APP DATE

H	REV. PER ECN 8809	Q.NO	15.2.79
G	REV. PER ECN 8539	Q.NO	22.9.88
F	REV. PER ECN 8197	Q.NO	11.12.85
D	REV. PER ECN 8197	Q.NO	5.1.83
C	REV. PER ECN 3641	Q.NO	26.9.80
B	REV. PER ECN 3153	Q.NO	11.12.79
A	REV. PER ECN 3070	Q.NO	24.10.79
PI	LTR	REVISION RECORD	APP DATE

DWG NO	826634	DESCRIPTION	AMP MODU II PIN HEADER
REVISION OF EACH ASSY NO		ITEM NO	H2
QTY REQD PER ASSY		PARTS LIST	
DIMENSIONS IN INCHES, TOLERANCES UNLESS OTHERWISE SPECIFIED:		MATERIAL	
2 PL DEC ±		HEAT TREAT	
3 PL DEC ±.006 (±0.15)		FINISH	
4 PL DEC ±		DR	9.1.79 H#
ANGLES ±		CHK	73.2.79 H#
SURF TEXTURE		REL	
REMOVE BURRS, BREAK SHARP EDGES .015R MAX		NAME	
		TE Connectivity	
		DWG NO	826634
		SHEET	H2